

Product Highlights

- High heat deflection
- Extremely impact resistant.
- Easy to use 1 : 1 mix ratio by volume for cartridge or meter mix dispensing
- User friendly work life
- Good viscosity and flow
- Meets UL 94 V-0 requirements

Mixing Properties:	Part A (Isocyanate)	Part B (Polyol)
Mix Ratio (Parts by Weight)	100	100
Mix Ratio (Parts by Volume)	100	100
Color	Light amber	Translucent
Viscosity cps @ 77F	200	400
Viscosity cps @ 77F (mixed)	350	
Specific Gravity @ 77F (mixed)	1.15	
Gel Time @77F	10 min ±1	
Demold Time (varies w/ mass)	2 hr @ RT / 30 min @ 180°F	

Physical Properties:	ASTM Method	Cure 1	Cure 2
Hardness, Shore D	D-2240	82 ± 3	82 ± 3
Flexural Modulus (PSI)	D-790	445,000	440,000
Tensile Strength (PSI)	D-638	9,800	10,200
Elongation (%)	D-638	10	10
IZOD Impact Notched (ft-lb/in)	D-256	1.8	1.8
Shrinkage (in/in) (10" sample)	D-2566	.003 ± .001	.003 ± .001
Heat Deflection Temperature (@ 66 PSI)	D-648	160°F	375°F
Color	Visual	Translucent amber	Translucent amber

Cure 1: Physical properties obtained using ambient room temperature (77°F). Tested after 7 days

Cure 2: Physical properties obtained with 4 hours at 185°F. Tested after 7 days.

Other related products offered

- Silicone rubber
- Mold release agents
- Mix tubes
- Additional products available. Inquire directly for products not listed.

Processing suggestions:

- Thoroughly agitate polyol (hardener) component to be sure the liquid is homogeneous.
- Properly weigh out the appropriate amounts of resin and hardener.
 - Mix Thoroughly for two minutes being sure to scrape sides and bottom of container.
 - For best results, de-air the product before pouring into mold.
 - Pressurize mold in a pressure pot at 60psi until cured.
 - Mold temperature is recommended to be 150 °F for faster de-mold, otherwise longer time in room temperature mold will be required.

Kit Sizes and Weights:

- | | |
|-------------------|----------|
| • Quart Kit | 4 lbs. |
| • Gallon Kit | 16 lbs. |
| • Five Gallon Kit | 80 lbs. |
| • Drum Kit | 900 lbs. |

Safety Precautions:

The safety data sheet (SDS) for this or any Thermoset Solutions, LLC product should be read prior to use and is available upon request from Thermoset Solutions, LLC.

Use in a ventilated area. Avoid contact with skin using protective gloves and protective clothing. Repeated or prolonged contact on the skin may cause an allergic reaction. Eye protection is extremely important. Always use approved safety glasses or goggles when handling this product.

If Contact Occurs:

- Eyes: Immediately flush with water for at least 15 minutes. Call a physician.
- Skin: Immediately wash with soap and water. Remove contaminated clothing. Do not use solvents to wash skin. Seek medical attention if allergic reaction occurs.
- Ingestion: If swallowed, call a physician immediately. Remove stomach contents by gastric suction or induce vomiting only as directed by medical personnel.

Notice:

The information contained in this tech data sheet is considered accurate. However, no warranty is expressed or implied regarding the accuracy of the data, the results to be obtained from the use thereof, or that any such use will not infringe upon a patent. User shall determine the suitability of the product for the intended application and assume all risk and liability whatsoever in connection therewith.